


#WeAreUV

group **alpna**
DRIVEN BY TECHNOLOGY

LAB-CURE




UV CURING EQUIPMENT FOR YOUR LABORATORY

CMYK INK COMPANY




www.alpna.in

INK LABORATORY




www.alpna.in

ARC + LED 2 in 1





***Floor Standing UV Curing System
For Lab Use***

- ▶ LED + ARC UV Lamp in One Compact Machine
- ▶ High Intensity LED UV / ARC Lamps
- ▶ Water Cooled LED UV
- ▶ Ideal for Ink Kitchen/Laboratry Use
- ▶ 180mm Curing width
- ▶ Full Function HMI Control





Compact Table Top



*Table Top - Compact UV
Curing System for Lab Use*

- ▶ 180mm Arc Length
- ▶ 1.8kw UV Lamp
- ▶ Single Phase Plug n Play
- ▶ Full Function HMI Control
- ▶ Adjustable Belt Speed with Display
- ▶ Ideal for Ink Kitchen/Laboratry Use



UV METER



This measuring instrument measures the applied dose thereby examining the effects of UV lamp aging and contamination. It can be used where a conveyor belt or similar, passes underneath UV lamps, e.g. in UV-curing 506.72 mm ovens, 1296.99 mm exposure systems, printed board exposure systems etc. which is typical in the furniture and printing industry, as well as PCB manufacturing and others.

#WeAreUV

UV LAMP DISPOSAL KIT

UV lamp service and safety kit

for lamp servicing and containing mercury spillages

All UV lamps contain a small amount of mercury. If spillages must be contained and cleared safely. To lamps should have the UV lamp service and safety kit station or workplace.

The UV lamp service and safety kit contains all the necessary instruments for changing lamps and is an excellent 'First Aid Kit' for lamp breakages. It deals with the small quantities of mercury with ease. A detailed and simple to understand manual is included.



ALPNA VISUAL PACKAGING AIDS

A-211, Okhla Industrial Area, Phase-I, New Delhi-110 020 | Tel: 011-41708792, 40574947 Email: enquiry@alpna.in